

Mask and Reticle Handling Products

A broad array of products for various mask and reticle sizes and styles



TABLE OF CONTENTS

Overview	1	Mask Carriers and Shipping Boxes	9
Lead Times and Minimum Order Quantities	1	A189 Series	9
Mask Packages	2	E Series	10
H68 Series	2	Miscellaneous Mask Carriers	12
H60 Series	3	Limited Warranty	14
H92 Series	4	For More Information	14
B80 Series	6	Terms and Conditions	14

OVERVIEW

Entegris offers a broad array of products for mask and reticle handling. Our portfolio provides secure mask protection and precise automation interface, increasing yields and minimizing unscheduled downtime.

For more information contact Entegris Customer Service at:
 +1 800 394 4083
 customerservice@entegris.com
www.entegris.com


LEAD TIMES AND MINIMUM ORDER QUANTITIES

Extended lead times and minimum order quantities apply on many of the products shown. For more information contact your local Entegris representative or Entegris customer service.

MASK PACKAGES

H68 SERIES

- For masks or reticles with pellicles
- Minimal contact
- Easy to open and close
- Easy removal
- Seal securely for protection
- Compact and stackable
- Roller hinge minimizes particle generation
- Optional latch security clip available



Part number	Mask size	Overall size	Notes	Material
H68-625-509-67C02 H68-03-67C02 clip	152 mm sq. x 6.4 mm (6.0" sq. x 0.25") or 127 mm sq. x 2.3 mm (5.0" sq. x 0.09")	208 mm sq. x 36 mm (8.2" sq. x 1.4")	Space available for identification labels Landing pads prevent tearing of pellicles Label wall for identification labels	STAT-PRO® 125 STAT-PRO 125
H68-600-67C02 H68-03-67C02 clip	127 mm sq. x 2.3 mm (5.0" sq. x 0.09") or 152 mm sq. x 3.1 mm (6.0" sq. x 0.12")	208 mm sq. x 36 mm (8.2" sq. x 1.4")	Space available for identification labels Landing pads prevent tearing of pellicles Label wall for identification labels Robotic compatible latch	STAT-PRO 125 STAT-PRO 125
H68-500-67C02 H68-03-67C02 clip	127 mm sq. x 2.3 mm (5.0" sq. x 0.09")	167 mm x 157 mm x 29 mm (6.6" x 6.2" x 1.1")	Holds 5X reticles with pellicles on both sides, including most Nikon, GCA, ASM and Canon	STAT-PRO 125 STAT-PRO 125
H68-100-67C02 H68-03-67C02 clip	27 mm x 76 mm x 2.3 mm (3.0" x 5.0" x 0.09")	145 mm x 115 mm x 17 mm (5.7" x 4.5" x .67")	Holds 1X reticles with pellicles on both sides and guides, including all types of Ultratech reticles Rounded guides minimize damage	STAT-PRO 125 STAT-PRO 125

H60 SERIES

- Holds one mask or reticle
- Manufactured and packaged in a cleanroom environment
- Bagged and sealed in a cleanroom bag and heat sealed in a second polyethylene bag
- Living hinge
- Compact and stackable
- Dustproof



Style A



Style B

Part number	Mask size	Overall size	Notes	Material
H60-60-09-0615 H60-60-09-67C02	152 mm sq. x 2.3 mm (6.0"sq. x 0.09")	162 mm sq. x 19 mm (6.4" sq. x 0.8")	Style A	Natural polypropylene STAT-PRO 125
H60-60-12-0615 H60-60-12-67C02	152 mm sq. x 3.00 mm (6.0" sq. x 0.12")	162 mm sq. x 19 mm (6.4" sq. x 0.8")	Style A	Natural polypropylene STAT-PRO 125
H60-60-15-0615 H60-60-15-67C02	152 mm sq. x 3.8 mm (6.0" sq. x 0.15")	162 mm sq. x 14 mm (6.4" sq. x 0.5")	Style A	Natural polypropylene STAT-PRO 125
H60-60-0615 H60-60-63A09	127 mm sq. or 152 mm sq. x 3.01 mm (5.0" sq. or 6.0" sq. x 0.12")	193 mm sq. x 28 mm (7.6" sq. x 1.1")	Style B	Natural polypropylene STAT-PRO 300
H60-51-0615 H60-51-63A09 H60-51-67C02	127 mm sq. x 2.3 mm (5.0" sq. x 0.09")	142 mm sq. x 15 mm (5.6" sq. x 0.6")	Style A	Natural polypropylene STAT-PRO 300 STAT-PRO 125
H60-50-0615 H60-50-67C02	127 mm sq. x 2.3 mm (5.0" sq. x 0.09")	142 mm sq. x 15 mm (5.6" sq. x 0.6")	Style A	Natural polypropylene STAT-PRO 125
H60-45-06-0615	114 mm sq. x 1.5 mm (4.5" sq. x 0.06")	124 mm sq. x 14 mm (4.9" sq. x 0.6")	Style A	Natural polypropylene
H60-40-06-0615 H60-40-06-67C02	102 mm sq. x 1.52 mm (4.0" sq. x 0.06")	117 mm sq. x 14 mm (4.6" sq. x 0.5")	Style A	Natural polypropylene STAT-PRO 125
H60-40-09-0615 H60-40-09-67C02	102 mm sq. x 2.3 mm (4.0" sq. x 0.09")	117 mm sq. x 14 mm (4.6" sq. x 0.5")	Style A	Natural polypropylene STAT-PRO 125
H60-3035-0615	76 mm sq. x 1.52 mm (3.0" sq. x 0.06") or 89 mm sq. x 1.52 mm (3.5" sq. x 0.06")	117 mm sq. x 20 mm (4.6" sq. x 0.8")	Style B	Natural polypropylene
H60-25-0615	64 mm sq. x 1.52 mm (2.5" sq. x 0.06")	96 mm x 71 mm x 18 mm (3.8" x 2.8" x 0.7")	Style B	Natural polypropylene

H92 SERIES

- Provide excellent security for masks or reticles with pellicles
- High impact resistance
- Stackable
- Easy to open and close
- Seal securely to provide a protective environment inside
- Label wall for identification label
- Additional materials and packages may be available on a special order basis



Mask Size: 178 mm sq. (7" sq.)

*Also holds 184.5 mm dia. with 177.8 mm flat
(7.25" dia. with 7" flat)*

Part number	Mask thickness	Overall size (L x W x H)	Space for pellicles	Component numbers	Material
H92-7012-108-1116	3.1 mm (0.12")	226 mm x 211 mm x 43 mm (8.9" x 8.3" x 1.7")	Double	H92-7012PL H92-7001PW	Clear polycarbonate
H92-7015-106-5413	3.8 mm (0.15")	226 mm x 211 mm x 24 mm (8.9" x 8.3" x 1.0")	None	H92-7001W	Clear Bayon™
H92-7015-108-5413	3.8 mm (0.15")	226 mm x 211 mm x 43 mm (8.9" x 8.3" x 1.7")	Double	H92-7001PW	Clear Bayon
H92-7025-106-1116	6.4 mm (0.25")	226 mm x 211 mm x 24 mm (8.9" x 8.3" x 1.0")	None	H92-7025L H92-7001W	Clear polycarbonate
H92-7025-108-1116	6.4 mm (0.25")	226 mm x 211 mm x 43 mm (8.9" x 8.3" x 1.7")	Double	H92-7025PL H92-7001PW	Clear polycarbonate

Brenda,
Note: some remaining part numbers shared content with the part numbers that were struck-through, so I left that content. (size, etc.)

Mask Size: 152 mm sq. (6" sq.)

Part number	Mask thickness	Overall size (L x W x H)	Space for pellicles	Component numbers	Material
H92-6009-106-1116 H92-6009-106-5413	2.3 mm (0.09")	191 mm x 179 mm x 22 mm (7.5" x 7.1" x 0.9")	None	H92-6009L H92-6001W	Clear polycarbonate Clear Bayon
H92-6012-108-1116	3.1 mm (0.12")	191 mm x 179 mm x 41 mm (7.5" x 7.1" x 1.6")	Double	H92-6012PL H92-6001PW	Clear polycarbonate
H92-6015-106-5413	3.8 mm (0.15")	191 mm x 179 mm x 22 mm (7.5" x 7.1" x 0.9")	None	H92-6015L H92-6001W	Clear Bayon
H92-6025-108-1116 H92-6025-108-5413	6.4 mm (0.25")	191 mm x 179 mm x 41 mm (7.5" x 7.1" x 1.6")	Double	H92-6025PL H92-6001PW	Clear polycarbonate Clear Bayon

Mask Size: 127 mm sq. (5" sq.)

Part number	Mask thickness	Overall size (L x W x H)	Space for pellicles	Component numbers	Material
H92-5009-106-5413	2.3 mm (0.09")	162 mm x 152 mm x 20 mm (6.4" x 6.0" x 0.8")	None	H92-5001W	Clear Bayon
H92-5009-108-5413	2.3 mm (0.09")	162 mm x 152 mm x 38 mm (6.4" x 6.0" x .15")	Double	H92-5001PW	Clear Bayon
H92-5091-108-1116 H92-5091-108-5413	2.3 mm (0.09")	191 mm x 179 mm x 41 mm (7.5" x 7.1" x 1.6")	Double	H92-6509PL H92-6501PW	Clear polycarbonate Clear Bayon
H92-5012-106-1116	3.1 mm (0.12")	162 mm x 152 mm x 20 mm (6.4" x 6.0" x .8")	None	H92-5012L H92-5001W	Clear polycarbonate
H92-5012-108-1116	3.1 mm (0.12")	162 mm x 152 mm x 38 mm (6.4" x 6.0" x 1.5")	Double	H92-5012PL H92-5001PW	Clear polycarbonate

B80 SERIES

- Provide excellent security for masks and reticles with pellicles
- High impact resistance
- Stackable
- Easy to open and close
- Seal securely to provide a protective environment inside
- Additional materials and packages may be available on a special order basis



Mask Size: 203 mm sq. (8" sq.)

Part number	Mask thickness	Overall size (L x W x H)	Space for pellicle	Label wall	Component numbers	Material
B8080-0100	2.3 mm (0.09")	236 mm x 249 mm x 25 mm (9.3" x 9.8" x 1.0")	None	No	B80-80-09 B80-80-01	Clear polycarbonate

Mask Size: 178 mm sq. (7" sq.)

Part number	Mask thickness	Overall size (L x W x H)	Space for pellicle	Label wall	Component numbers	Material
B8070-0300	3.1 mm (0.12")	234 mm x 246 mm x 25 mm (9.2" x 9.7" x 1.0")	None	No	B80-70-12 B80-70-01	Clear polycarbonate
B8070-0104	3.8 mm (0.15")	234 mm x 246 mm x 25 mm (9.2" x 9.7" x 1.0")	None	No	B80-70-15 B80-70-01	Clear Bayon
B8070-0200	6.4 mm (0.25")	234 mm x 246 mm x 25 mm (9.2" x 9.7" x 1.0")	None	No	B80-70-25 B80-70-01	Clear polycarbonate

Mask Size: 152 mm sq. (6" sq.)

Part number	Mask thickness	Overall size (L x W x H)	Space for pellicle	Label wall	Component numbers	Material
B8060-0611	2.3 mm (0.09")	185 mm x 180 mm x 23 mm (7.3" x 7.1" x 0.9")	None	Yes	B80-60-09 B80-60-01A	Amber antistatic ABS
B8060-2011	2.3 mm (0.09")	185 mm x 180 mm x 41 mm (7.3" x 7.1" x 1.6")	Double	Yes	B80-60P-09 B80-60P-01A	Amber antistatic ABS
B8060-0700	3.1 mm (0.12")	185 mm x 180 mm x 23 mm (7.3" x 7.1" x 0.9")	None	Yes	B80-60-12 B80-60-01A	Clear polycarbonate
B8060-1900	3.1 mm (0.12")	185 mm x 180 mm x 41 mm (7.3" x 7.1" x 1.6")	Double	Yes	B80-60P-12 B80-60P-01A	Clear polycarbonate
B8060-1911	3.1 mm (0.12")	185 mm x 180 mm x 41 mm (7.3" x 7.1" x 1.6")	Double	Yes	B80-60P-12 B80-60P-01A	Amber antistatic ABS
B8060-2211	6.4 mm (0.25")	185 mm x 180 mm x 41 mm (7.3" x 7.1" x 1.6")	Double	Yes	B80-60P-25 B80-60P-02A	Amber antistatic ABS

Mask Size: 127 mm Sq. (5" sq.)

Part number	Mask thickness	Overall size (L x W x H)	Space for pellicle	Label wall	Component numbers	Material
B7950-0100	2.3 mm (0.09")	160 mm x 157 mm x 20 mm (6.3" x 6.2" x 0.8")	None	Yes	B80-50-09 B80-50-01A	Clear polycarbonate
B8050-0600	2.3 mm (0.09")	160 mm x 157 mm x 20 mm (6.3" x 6.2" x 0.8")	None	Yes	B80-50-09 B80-50-01A	Clear polycarbonate
B8050-1600	2.3 mm (0.09")	160 mm x 157 mm x 38 mm (6.3" x 6.2" x 1.5")	Double	Yes	B80-50P-09 B80-50P-01A	Clear polycarbonate
B8050-1611	2.3 mm (0.09")	160 mm x 157 mm x 38 mm (6.3" x 6.2" x 1.5")	Double	Yes	B80-50P-09 B80-50P-01A	Amber antistatic ABS
B8060-2400	2.3 mm (0.09")	185 mm x 180 mm x 41 mm (7.3" x 7.1" x 1.6")	Large 5" double	Yes	B80-6SP-09 B80-6SP-01A	Clear polycarbonate
B8060-2403	2.3 mm (0.09")	185 mm x 180 mm x 41 mm (7.3" x 7.1" x 1.6")	Large 5" double	Yes	B80-6SP-09 B80-6SP-01A	Clear Bayon
B-8060-2411	2.3 mm (0.09")	185 mm x 180 mm x 41 mm (7.3" x 7.1" x 1.6")	Large 5" double	Yes	B80-6SP-09 B80-6SP-01A	Amber antistatic ABS

Mask Size: 102 mm sq. (4" sq.)

Part number	Mask thickness	Overall size (L x W x H)	Space for pellicle	Label wall	Component numbers	Material
B8040-0811	1.5 mm (0.06")	160 mm x 157 mm x 38 mm (6.3" x 6.2" x 1.5")	Double	Yes	B80-40P-06 B80-40P-01A	Amber antistatic ABS

Mask Size: 76 mm x 127 mm (3" x 5")

Part number	Mask thickness	Overall size (L x W x H)	Space for pellicle	Label wall	Component numbers	Material
B8035-0200	2.3 mm (0.09")	160 mm x 157 mm x 20 mm (6.3" x 6.2" x 0.8")	None	Yes	B80-35-09 B80-35-01A	Clear polycarbonate
B8035-0204	2.3 mm (0.09")	160 mm x 157 mm x 20 mm (6.3" x 6.2" x 0.8")	None	Yes	B80-35-09 B80-35-01A	Clear Bayon
B8035-0211	2.3 mm (0.09")	160 mm x 157 mm x 20 mm (6.3" x 6.2" x 0.8")	None	Yes	B80-35-09 B80-35-01A	Amber antistatic ABS


Mask Size: 76 mm sq. (3" sq.)

Part number	Mask thickness	Overall size (L x W x H)	Space for pellicle	Label wall	Component numbers	Material
B8030-0211	1.5 mm (0.06")	135 mm x 127 mm x 20 mm (5.3" x 5.0" x 0.8")	None	Yes	B80-30-06 B80-30-01A	Amber antistatic ABS

MASK CARRIERS AND SHIPPING BOXES

A189 SERIES

- For masks or reticles
- Fluoroelastomer cushions on the inside of the cover included with ABS shipping box assembly
- Carriers, boxes, and handles purchased separately



Part number	Mask size	Capacity	Pocket spacing	Pocket flat	Carrier overall size	Box overall size	Material
A189-70-15-0715 carrier E94-70-101-1403 box A058-70-0515 handle	178 mm sq. (7.0" sq.)	10	13 mm (0.5")	4.2 mm (0.17")	157 mm × 201 mm × 163 mm (6.2" × 7.9" × 6.4")	208 mm × 234 mm × 206 mm (8.2" × 9.2" × 8.1")	High density polyethylene Blue ABS PVDF
A189-60-15-0715 carrier E94-60-101-1403 box A058-60-0515 handle	152 mm sq. (6.0" sq.)	10	13 mm (0.5")	4.2 mm (0.17")	157 mm × 175 mm × 137 mm (6.2" × 6.9" × 5.4")	208 mm × 211 mm × 180 mm (8.2" × 8.3" × 7.1")	High density polyethylene Blue ABS PVDF
A189-60-25-0715 carrier E94-60-101-1403 box A058-60-0515 handle	152 mm sq. (6.0" sq.)	10	13 mm (0.5")	6.7 mm (0.27")	157 mm × 175 mm × 137 mm (6.2" × 6.9" × 5.4")	208 mm × 211 mm × 180 mm (8.2" × 8.3" × 7.1")	High density polyethylene Blue ABS PVDF
A189-50-12-0715 carrier E94-50-101-1403 box A058-50-0515 handle	127 mm sq. (5.0" sq.)	20	6.4 mm (0.25")	3.4 mm (0.14")	157 mm × 147 mm × 112 mm (6.2" × 5.8" × 4.4")	196 mm × 173 mm × 155 mm (7.7" × 6.8" × 6.1")	High density polyethylene Blue ABS PVDF
A189-45-12-0715 carrier E94-45-101-1403 box A058-45-0515 handle	114 mm sq. (4.5" sq.)	20	6.4 mm (0.25")	3.1 mm (0.12")	157 mm × 135 mm × 112 mm (6.2" × 5.3" × 4.4")	196 mm × 173 mm × 155 mm (7.7" × 6.8" × 6.1")	High density polyethylene Blue ABS PVDF
A189-40-09-0715 carrier E94-40-101-1403 box A058-40-0515 handle	102 mm sq. (4.0" sq.)	20	6.4 mm (0.25")	2.5 mm (0.10")	157 mm × 124 mm × 81 mm (6.2" × 4.9" × 3.2")	196 mm × 145 mm × 124 mm (7.7" × 5.7" × 4.9")	High density polyethylene Blue ABS PVDF
A189-35-09-0715 carrier	89 mm sq. (3.5" sq.)	20	6.4 mm (0.25")	2.5 mm (0.10")	157 mm × 112 mm × 81 mm (6.2" × 4.4" × 3.2")	–	High density polyethylene
A189-30-09-0715 carrier E94-30-101-1403 box A058-30-0515 handle	76 mm sq. (3.0" sq.)	20	6.4 mm (0.25")	2.5 mm (0.10")	157 mm × 99 mm × 81 mm (6.2" × 3.9" × 3.2")	196 mm × 145 mm × 112 mm (7.7" × 5.7" × 4.4")	High density polyethylene Blue ABS PVDF
A189-25-09-0715 carrier E94-25-101-1403 box A058-25-0515 handle	64 mm sq. (2.5" sq.)	20	6.4 mm (0.25")	2.5 mm (0.10")	157 mm × 89 mm × 56 mm (6.2" × 3.5" × 2.2")	196 mm × 119 mm × 86 mm (7.7" × 4.7" × 3.4")	High density polyethylene Blue ABS PVDF
A189-20-09-0715 carrier A058-20-0515 handle	51 mm sq. (2.0" sq.)	20	6.4 mm (0.25")	2.5 mm (0.10")	157 mm × 74 mm × 56 mm (6.2" × 2.9" × 2.2")	–	High density polyethylene PVDF

E SERIES


- For masks or reticles
- Carriers and boxes purchased as an assembly



Part number	Mask size	Capacity	Pocket spacing	Pocket flat	Carrier overall size	Box overall size	Carrier material	Box material
E05-0002 assembly	51 mm sq. (2.0" sq.)	30	6.7 mm (0.26")	2.5 mm (0.10")	222 mm x 59 mm x 51 mm (8.8" x 2.3" x 2.0")	257 mm x 89 mm x 93 mm (10.1" x 3.5" x 3.6")	High density polyethylene	Medium impact polystyrene
E05-0001 assembly	64 mm sq. (2.5" sq.)	30	6.7 mm (0.26")	2.5 mm (0.10")	222 mm x 71 mm x 67 mm (8.8" x 2.8" x 2.6")	257 mm x 89 mm x 93 mm (10.1" x 3.5" x 3.6")	Polypropylene	Medium impact polystyrene
E01-0001 assembly	76 mm sq. (3.0" sq.)	30	6.7 mm (0.26")	2.5 mm (0.10")	222 mm x 84 mm x 73 mm (8.8" x 3.3" x 2.9")	256 mm x 116 mm x 117 mm (10.0" x 4.6" x 4.6")	Polypropylene	Medium impact polystyrene
E01-0003 assembly	76 mm sq. (3.0" sq.)	30	6.7 mm (0.26")	2.5 mm (0.10")	222 mm x 84 mm x 73 mm (8.8" x 3.3" x 2.9")	256 mm x 116 mm x 117.2 mm (10.0" x 4.6" x 4.6")	High density polyethylene	Medium impact polystyrene
E09-0002 assembly	102 mm sq. (4.0" sq.)	30	6.7 mm (0.26")	2.5 mm (0.10")	225 mm x 113 mm x 89 mm (8.9" x 4.5" x 3.5")	257 mm x 133.4 mm x 127 mm (10.1" x 5.3" x 5.0")	High density polyethylene	Medium impact polystyrene
E09-0003 assembly	102 mm sq. (4.0" sq.)	30	6.7 mm (0.25")	2.5 mm (0.10")	225 mm x 113 mm x 89 mm (8.9" x 4.5" x 3.5")	257 mm x 133.4 mm x 126.8 mm (10.1" x 5.3" x 5.0")	Polypropylene	Medium impact polystyrene

Part number	Mask size	Capacity	Pocket spacing	Pocket flat	Carrier overall size	Box overall size	Carrier material	Box material
E55-0001 assembly	127 mm sq. (5.0" sq.)	20	6.4 mm (0.25")	3.8 mm (0.15")	174 mm × 149 mm × 101 mm (6.8" × 5.9" × 4.0")	218 mm × 181 mm × 157 mm (8.6" × 7.1" × 6.2")	Polypropylene	Medium impact polystyrene
E55-0003 assembly	127 mm sq. (5.0" sq.)	20	6.4 mm (0.25")	3.2 mm (0.13")	174 mm × 149 mm × 101 mm (6.8" × 5.9" × 4.0")	218 mm × 181 mm × 157 mm (8.6" × 7.1" × 6.2")	High density polyethylene	Medium impact polystyrene
E56-0002 assembly	152 mm sq. (6.0" sq.)	20	6.4 mm (0.25")	2.5 mm (0.10")	174 mm × 175 mm × 123 mm (6.8" × 6.9" × 4.8")	218 mm × 206 mm × 183 mm (8.6" × 8.1" × 7.2")	Polypropylene	Medium impact polystyrene
E56-0004 assembly	152 mm sq. (6.0" sq.)	20	6.4 mm (0.25")	2.5 mm (0.10")	174 mm × 175 mm × 123 mm (6.8" × 6.9" × 4.8")	218 mm × 206 mm × 183 mm (8.6" × 8.1" × 7.2")	High density polyethylene	Medium impact polystyrene
E56-0005 assembly	152 mm sq. (6.0" sq.)	20	6.4 mm (0.25")	3.8 mm (0.15")	174 mm × 175 mm × 123 mm (6.8" × 6.9" × 4.8")	218 mm × 206 mm × 183 mm (8.6" × 8.1" × 7.2")	High density polyethylene	Medium impact polystyrene
E56-0006 assembly	152 mm sq. (6.0" sq.)	20	6.4 mm (0.25")	3.8 mm (0.15")	174 mm × 175 mm × 123 mm (6.8" × 6.9" × 4.8")	218 mm × 206 mm × 183 mm (8.6" × 8.1" × 7.2")	Polypropylene	Medium impact polystyrene

MISCELLANEOUS MASK CARRIERS



Part number	Mask size	Capacity	Pocket spacing	Pocket flat	Handle	Overall size	Notes	Material
A108-50-0215	127 mm sq. (5.0" sq.)	20	6.4 mm (0.25")	3.2 mm (0.13")	A047-0215, A72-50-03-0215	159 mm × 149 mm × 15 mm (6.3" × 5.9" × 5.7")	Automation compatible Wash openings	PFA
K50-0003	127 mm sq. (5.0" sq.)	11	5.1 mm (0.20")	2.8 mm (0.11")	–	136 mm × 83 mm × 138 mm (5.3" × 3.3" × 5.5")	Pockets molded into box sides	Clear Bayon
K50-0001	127 mm sq. (5.0" sq.)	11	5.1 mm (0.20")	2.8 mm (0.11")	–	136 mm × 83 mm × 138 mm (5.3" × 3.3" × 5.5")	Pockets molded into box sides	Amber antistatic ABS
A108-30-0215	76 mm sq. (3.0" sq.)	20	6.4 mm (0.25")	3.2 mm (0.13")	–	159 mm × 98 mm × 99 mm (6.3" × 3.9" × 3.9")	Automation compatible Wash openings Compatible box: E94-40-101-1403	PFA
A102-01-0315 A102-01-0603	51 mm sq. (2.0" sq.)	25	4.8 mm (0.19")	1.0 mm (0.04")	–	142 mm × 69 mm × 64 mm (5.6" × 2.7" × 2.5")	Automation compatible	ETFE Blue polypropylene
A41-01-0215 A41-01-0603	51 mm sq. (2.0" sq.)	12	4.0 mm (0.16")	–	–	76 mm × 61 mm × 33 mm (3.0" × 2.4" × 1.7")	Deep "V" slots hold various thicknesses	PFA Blue polypropylene

Part number	Mask size	Capacity	Pocket spacing	Pocket flat	Handle	Overall size	Notes	Material
A67-01-0603	51 mm sq. (2.0" sq.)	25	3.2 mm (0.13")	1.6 mm (0.06")	–	107 mm × 61 mm × 36 mm (4.2" × 2.4" × 1.4")	–	Blue polypro- pylene
A66-0603	25 mm sq. (1.0" sq.)	25	3.2 mm (0.13")	1.6 mm (0.06")	–	107 mm × 36 mm × 28 mm (4.2" × 1.4" × 1.1")	–	Blue polypro- pylene
A19-01-0215 A19-01-0603	9.5 – 50.8 mm sq. (0.38" – 1.0" sq.)	40	–	–	A01, A029	150 mm × 107 mm × 46 mm (5.9" × 4.2" × 1.8")	–	PFA Blue polypro- pylene

LIMITED WARRANTY

Entegris' products are subject to the Entegris, Inc. General Limited Warranty. To view and print this information, visit [entegris.com](https://www.entegris.com) and select the [Legal & Trademark Notices](#) link in the footer. Entegris does not warrant any failure in the case of customers using unapproved foreign components.

FOR MORE INFORMATION

Please call your Regional Customer Service Center today to learn what Entegris can do for you. Visit [entegris.com](https://www.entegris.com) and select the [Contact Us](#) link to find the customer service center nearest you.

TERMS AND CONDITIONS OF SALE

All purchases are subject to Entegris' Terms and Conditions of Sale. To view and print this information, visit [entegris.com](https://www.entegris.com) and select the [Terms & Conditions](#) link in the footer.



Corporate Headquarters

129 Concord Road
Billerica, MA 01821
USA

Customer Service

Tel +1 952 556 4181
Fax +1 952 556 8022
Toll Free 800 394 4083

Entegris®, the Entegris Rings Design®, and other product names are trademarks of Entegris, Inc. as listed on [entegris.com/trademarks](https://www.entegris.com/trademarks). All third-party product names, logos, and company names are trademarks or registered trademarks of their respective owners. Use of them does not imply any affiliation, sponsorship, or endorsement by the trademark owner.

©2002-2024 Entegris, Inc. | All rights reserved. | Printed in the USA | 1170-0984ENT-0824